

Single Bay Mobile 19" EIA Server Rack Cabinet

SERVERPRO™ 4X SERIES

IP66

NEMA 4X

Applications

NEMACO™'s NEMA 4X stainless steel mobile 19" rack enclosures are built for corrosive environments that also require repositionable rack protection without structural modification. Rear straight caster wheels and front swivel caster wheels with locking brakes allow free movement across concrete slabs and raised equipment floors, then lock in place for stable stationary operation. Available in 304 and 316L stainless steel, they are suited for coastal installations, chemical processing facilities, wastewater treatment plants, food and beverage production environments, and any deployment where salt air, chemical wash, or persistent moisture demands more than a powder-coated enclosure -- with the added flexibility of a mobile chassis.

These enclosures are deployed across security and surveillance systems, radar installations, SCADA and process control networks, satellite telecom infrastructure, power plants, fiber optic nodes, and data acquisition systems for commercial and military applications. The dual-door configuration provides independent front and rear access without repositioning the cabinet, with both doors opening to a full 135 degrees.

Industry Standard

- UL 50 and UL 50E; File Number E507642
- cUL Listed per CSA C22.2 No. 94; File Number E507642
- CSA C22.2 No. 94.1-15 and 94.2-15
- NEMA/EEMAC: Types 4, 4X, and 12
- IEC 60529 Type IP66

Specifications

NEMA 4/12 (IP66) rated

NEMA 4 gasket door seal for water resistance

NEMA 4-rated door hardware and latches

Precision-fit door with foam-in-place gasket and easy-turn latch

Continuous welded enclosure corner seams

12-gauge steel on enclosures 60" tall and above

14-gauge steel on enclosures under 60" tall

EIA-standard 19" rack rails in 12-gauge coated steel

#10-32 tapped holes on rack rails (powder coated)

Fully adjustable rack system with sliding rack rail tracks

2-post and 4-post rack rail configurations available

1/4-20 x 3/4 interior ground studs on enclosure door and body

Foam-in-place gasket, 1.25" wide

Heavy-duty 3-point latch padlock handle

Padlockable hasp and staple

Heavy-duty stainless door hinge, removable

Lifting pad-eyes welded to top

Front swivel caster wheels with locking brake; rear straight caster wheels

5
YEARS

LIMITED PRODUCT
WARRANTY



Standard Features

Mobile Caster System

Front swivel caster wheels with locking brake and rear straight caster wheels allow free repositioning across concrete and raised floors, with positive locking for stable stationary operation

Dual-Door Access

Self-supporting on concrete slabs, raised floors, or outdoor pads with no wall anchoring required

304 and 316L Stainless Steel

304 stainless standard for corrosion-resistant applications; 316L available for coastal, chemical, and high-chloride environments

Fully Adjustable Rack System

19" EIA adjustable rack rails with sliding depth adjustment to accommodate varying equipment configurations

Precision Door Seal

NEMA 4 gasket door seal with precision-fit door and easy-turn latch for consistent water resistance

Fully Welded Seams

All corner seams are continuously welded and ground smooth for a clean, sealed enclosure

Ground Studs

1/4-20 ground studs on door and body for proper bonding and grounding


Heavy-Duty Hardware

3-point latch padlock handles with heavy-duty lifting pads welded to top

Radiant Barrier Insulation

Standard 1/2" thick (R3.2) insulation provides thermal protection for outdoor installations

Reference



Part Number Decoder

N4

24

24

24

-

F

2D

CS

19

RATING

N4 - NEMA 4 N4X - NEMA 4X

HEIGHT (inch)

Available Options: 24 , 30 , 36 , 42 , 48 , 54 , 60 , 66 , 72

WIDTH (inch)

Available Options: 24

DEPTH (inch)

Available Options: 24 , 30 , 36 , 42

TYPE

19 - 19" EIA Rack System

MATERIAL

CS - Coated Steel AL - Coated Aluminum
S4 - 304 Stainless Steel S6 - 316 Stainless Steel

DOOR

1D - 1 Front Door 2D - 1 Front and 1 Rear Door

MOUNTING

W - Wall Mount F - Floor Mount FS - Free Standing M - Mobile

Drawing Table (304 Stainless Steel)

Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front	16D	N4X242416-M1DS419	12 RU	24	24	16	14.5	19" EIA	304SS	14 ga.	Mobile	127.66
Front		N4X302416-M1DS419	15 RU	30	24	16	14.5	19" EIA	304SS	14 ga.	Mobile	142.73
Front		N4X362416-M1DS419	18 RU	36	24	16	14.5	19" EIA	304SS	14 ga.	Mobile	155.53
Front		N4X422416-M1DS419	22 RU	42	24	16	14.5	19" EIA	304SS	14 ga.	Mobile	169.19
Front		N4X482416-M1DS419	25 RU	48	24	16	14.5	19" EIA	304SS	14 ga.	Mobile	215
Front		N4X542416-M1DS419	29 RU	54	24	16	14.5	19" EIA	304SS	14 ga.	Mobile	231.94
Front		N4X602416-M1DS419	32 RU	60	24	16	14.5	19" EIA	304SS	14 ga.	Mobile	247.92
Front		N4X662416-M1DS419	36 RU	66	24	16	14.5	19" EIA	304SS	14 ga.	Mobile	269.57
Front		N4X722416-M1DS419	39 RU	72	24	16	14.5	19" EIA	304SS	14 ga.	Mobile	286.08

Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front	20D	N4X242420-M1DS419	12 RU	24	24	20	18.5	19" EIA	304SS	14 ga.	Mobile	141.95
Front		N4X302420-M1DS419	15 RU	30	24	20	18.5	19" EIA	304SS	14 ga.	Mobile	159.87
Front		N4X362420-M1DS419	18 RU	36	24	20	18.5	19" EIA	304SS	14 ga.	Mobile	174.01
Front		N4X422420-M1DS419	22 RU	42	24	20	18.5	19" EIA	304SS	14 ga.	Mobile	188.17
Front		N4X482420-M1DS419	25 RU	48	24	20	18.5	19" EIA	304SS	14 ga.	Mobile	237.87
Front		N4X542420-M1DS419	29 RU	54	24	20	18.5	19" EIA	304SS	14 ga.	Mobile	256.1
Front		N4X602420-M1DS419	32 RU	60	24	20	18.5	19" EIA	304SS	14 ga.	Mobile	273.38
Front		N4X662420-M1DS419	36 RU	66	24	20	18.5	19" EIA	304SS	14 ga.	Mobile	297.75
Front		N4X722420-M1DS419	39 RU	72	24	20	18.5	19" EIA	304SS	14 ga.	Mobile	314.12
Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front	24D	N4X242424-M1DS419	12 RU	24	24	24	22.5	19" EIA	304SS	14 ga.	Mobile	153.41
Front		N4X302424-M1DS419	15 RU	30	24	24	22.5	19" EIA	304SS	14 ga.	Mobile	173.3
Front		N4X362424-M1DS419	18 RU	36	24	24	22.5	19" EIA	304SS	14 ga.	Mobile	188.64
Front		N4X422424-M1DS419	22 RU	42	24	24	22.5	19" EIA	304SS	14 ga.	Mobile	204.76
Front		N4X482424-M1DS419	25 RU	48	24	24	22.5	19" EIA	304SS	14 ga.	Mobile	257.74
Front		N4X542424-M1DS419	29 RU	54	24	24	22.5	19" EIA	304SS	14 ga.	Mobile	277.28
Front		N4X602424-M1DS419	32 RU	60	24	24	22.5	19" EIA	304SS	14 ga.	Mobile	295.86
Front		N4X662424-M1DS419	36 RU	66	24	24	22.5	19" EIA	304SS	14 ga.	Mobile	322.93
Front		N4X722424-M1DS419	39 RU	72	24	24	22.5	19" EIA	304SS	14 ga.	Mobile	340.6
Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front	30D	N4X242430-M1DS419	12 RU	24	24	30	28.5	19" EIA	304SS	14 ga.	Mobile	170.59
Front		N4X302430-M1DS419	15 RU	30	24	30	28.5	19" EIA	304SS	14 ga.	Mobile	192.1
Front		N4X362430-M1DS419	18 RU	36	24	30	28.5	19" EIA	304SS	14 ga.	Mobile	209.07
Front		N4X422430-M1DS419	22 RU	42	24	30	28.5	19" EIA	304SS	14 ga.	Mobile	226.82
Front		N4X482430-M1DS419	25 RU	48	24	30	28.5	19" EIA	304SS	14 ga.	Mobile	286.59
Front		N4X542430-M1DS419	29 RU	54	24	30	28.5	19" EIA	304SS	14 ga.	Mobile	308.08
Front		N4X602430-M1DS419	32 RU	60	24	30	28.5	19" EIA	304SS	14 ga.	Mobile	328.61
Front		N4X662430-M1DS419	36 RU	66	24	30	28.5	19" EIA	304SS	14 ga.	Mobile	359.74
Front		N4X722430-M1DS419	39 RU	72	24	30	28.5	19" EIA	304SS	14 ga.	Mobile	379.36
Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front/Rear	24D	N4X242424-M2DS419	12 RU	24	24	24	21	19" EIA	304SS	14 ga.	Mobile	167.34
Front/Rear		N4X302424-M2DS419	15 RU	30	24	24	21	19" EIA	304SS	14 ga.	Mobile	188.72
Front/Rear		N4X362424-M2DS419	18 RU	36	24	24	21	19" EIA	304SS	14 ga.	Mobile	205.55
Front/Rear		N4X422424-M2DS419	22 RU	42	24	24	21	19" EIA	304SS	14 ga.	Mobile	223.13
Front/Rear		N4X482424-M2DS419	25 RU	48	24	24	21	19" EIA	304SS	14 ga.	Mobile	280.52
Front/Rear		N4X542424-M2DS419	29 RU	54	24	24	21	19" EIA	304SS	14 ga.	Mobile	301.95
Front/Rear		N4X602424-M2DS419	32 RU	60	24	24	21	19" EIA	304SS	14 ga.	Mobile	322.27
Front/Rear		N4X662424-M2DS419	36 RU	66	24	24	21	19" EIA	304SS	14 ga.	Mobile	351.93
Front/Rear		N4X722424-M2DS419	39 RU	72	24	24	21	19" EIA	304SS	14 ga.	Mobile	371.35
Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front/Rear	30D	N4X242430-M2DS419	12 RU	24	24	30	27	19" EIA	304SS	14 ga.	Mobile	184.52
Front/Rear		N4X302430-M2DS419	15 RU	30	24	30	27	19" EIA	304SS	14 ga.	Mobile	207.53
Front/Rear		N4X362430-M2DS419	18 RU	36	24	30	27	19" EIA	304SS	14 ga.	Mobile	225.98
Front/Rear		N4X422430-M2DS419	22 RU	42	24	30	27	19" EIA	304SS	14 ga.	Mobile	245.19
Front/Rear		N4X482430-M2DS419	25 RU	48	24	30	27	19" EIA	304SS	14 ga.	Mobile	309.37
Front/Rear		N4X542430-M2DS419	29 RU	54	24	30	27	19" EIA	304SS	14 ga.	Mobile	332.76
Front/Rear		N4X602430-M2DS419	32 RU	60	24	30	27	19" EIA	304SS	14 ga.	Mobile	355.03
Front/Rear		N4X662430-M2DS419	36 RU	66	24	30	27	19" EIA	304SS	14 ga.	Mobile	388.75
Front/Rear		N4X722430-M2DS419	39 RU	72	24	30	27	19" EIA	304SS	14 ga.	Mobile	410.11

Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front/Rear	36D	N4X242436-M2DS419	12 RU	24	24	36	33	19" EIA	304SS	14 ga.	Mobile	201.7
Front/Rear		N4X302436-M2DS419	15 RU	30	24	36	33	19" EIA	304SS	14 ga.	Mobile	226.33
Front/Rear		N4X362436-M2DS419	18 RU	36	24	36	33	19" EIA	304SS	14 ga.	Mobile	246.41
Front/Rear		N4X422436-M2DS419	22 RU	42	24	36	33	19" EIA	304SS	14 ga.	Mobile	267.25
Front/Rear		N4X482436-M2DS419	25 RU	48	24	36	33	19" EIA	304SS	14 ga.	Mobile	338.23
Front/Rear		N4X542436-M2DS419	29 RU	54	24	36	33	19" EIA	304SS	14 ga.	Mobile	363.57
Front/Rear		N4X602436-M2DS419	32 RU	60	24	36	33	19" EIA	304SS	14 ga.	Mobile	387.79
Front/Rear		N4X662436-M2DS419	36 RU	66	24	36	33	19" EIA	304SS	14 ga.	Mobile	425.57
Front/Rear		N4X722436-M2DS419	39 RU	72	24	36	33	19" EIA	304SS	14 ga.	Mobile	448.88
Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front/Rear	42D	N4X242442-M2DS419	12 RU	24	24	42	39	19" EIA	304SS	14 ga.	Mobile	218.88
Front/Rear		N4X302442-M2DS419	15 RU	30	24	42	39	19" EIA	304SS	14 ga.	Mobile	245.14
Front/Rear		N4X362442-M2DS419	18 RU	36	24	42	39	19" EIA	304SS	14 ga.	Mobile	266.84
Front/Rear		N4X422442-M2DS419	22 RU	42	24	42	39	19" EIA	304SS	14 ga.	Mobile	289.31
Front/Rear		N4X482442-M2DS419	25 RU	48	24	42	39	19" EIA	304SS	14 ga.	Mobile	367.09
Front/Rear		N4X542442-M2DS419	29 RU	54	24	42	39	19" EIA	304SS	14 ga.	Mobile	394.37
Front/Rear		N4X602442-M2DS419	32 RU	60	24	42	39	19" EIA	304SS	14 ga.	Mobile	420.55
Front/Rear		N4X662442-M2DS419	36 RU	66	24	42	39	19" EIA	304SS	14 ga.	Mobile	462.39
Front/Rear		N4X722442-M2DS419	39 RU	72	24	42	39	19" EIA	304SS	14 ga.	Mobile	487.65

Drawing Table

Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front	16D	N4X242416-M1DS619	12 RU	24	24	16	14.5	19" EIA	316SS	14 ga.	Mobile	127.66
Front		N4X302416-M1DS619	15 RU	30	24	16	14.5	19" EIA	316SS	14 ga.	Mobile	142.73
Front		N4X362416-M1DS619	18 RU	36	24	16	14.5	19" EIA	316SS	14 ga.	Mobile	155.53
Front		N4X422416-M1DS619	22 RU	42	24	16	14.5	19" EIA	316SS	14 ga.	Mobile	169.19
Front		N4X482416-M1DS619	25 RU	48	24	16	14.5	19" EIA	316SS	14 ga.	Mobile	215
Front		N4X542416-M1DS619	29 RU	54	24	16	14.5	19" EIA	316SS	14 ga.	Mobile	231.94
Front		N4X602416-M1DS619	32 RU	60	24	16	14.5	19" EIA	316SS	14 ga.	Mobile	247.92
Front		N4X662416-M1DS619	36 RU	66	24	16	14.5	19" EIA	316SS	14 ga.	Mobile	269.57
Front		N4X722416-M1DS619	39 RU	72	24	16	14.5	19" EIA	316SS	14 ga.	Mobile	286.08
Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front	20D	N4X242420-M1DS619	12 RU	24	24	20	18.5	19" EIA	316SS	14 ga.	Mobile	141.95
Front		N4X302420-M1DS619	15 RU	30	24	20	18.5	19" EIA	316SS	14 ga.	Mobile	159.87
Front		N4X362420-M1DS619	18 RU	36	24	20	18.5	19" EIA	316SS	14 ga.	Mobile	174.01
Front		N4X422420-M1DS619	22 RU	42	24	20	18.5	19" EIA	316SS	14 ga.	Mobile	188.17
Front		N4X482420-M1DS619	25 RU	48	24	20	18.5	19" EIA	316SS	14 ga.	Mobile	237.87
Front		N4X542420-M1DS619	29 RU	54	24	20	18.5	19" EIA	316SS	14 ga.	Mobile	256.1
Front		N4X602420-M1DS619	32 RU	60	24	20	18.5	19" EIA	316SS	14 ga.	Mobile	273.38
Front		N4X662420-M1DS619	36 RU	66	24	20	18.5	19" EIA	316SS	14 ga.	Mobile	297.75
Front		N4X722420-M1DS619	39 RU	72	24	20	18.5	19" EIA	316SS	14 ga.	Mobile	314.12
Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front	24D	N4X242424-M1DS619	12 RU	24	24	24	22.5	19" EIA	316SS	14 ga.	Mobile	153.41
Front		N4X302424-M1DS619	15 RU	30	24	24	22.5	19" EIA	316SS	14 ga.	Mobile	173.3
Front		N4X362424-M1DS619	18 RU	36	24	24	22.5	19" EIA	316SS	14 ga.	Mobile	188.64
Front		N4X422424-M1DS619	22 RU	42	24	24	22.5	19" EIA	316SS	14 ga.	Mobile	204.76
Front		N4X482424-M1DS619	25 RU	48	24	24	22.5	19" EIA	316SS	14 ga.	Mobile	257.74
Front		N4X542424-M1DS619	29 RU	54	24	24	22.5	19" EIA	316SS	14 ga.	Mobile	277.28
Front		N4X602424-M1DS619	32 RU	60	24	24	22.5	19" EIA	316SS	14 ga.	Mobile	295.86
Front		N4X662424-M1DS619	36 RU	66	24	24	22.5	19" EIA	316SS	14 ga.	Mobile	322.93
Front		N4X722424-M1DS619	39 RU	72	24	24	22.5	19" EIA	316SS	14 ga.	Mobile	340.6

Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front	30D	N4X242430-M1DS619	12 RU	24	24	30	28.5	19" EIA	316SS	14 ga.	Mobile	170.59
Front		N4X302430-M1DS619	15 RU	30	24	30	28.5	19" EIA	316SS	14 ga.	Mobile	192.1
Front		N4X362430-M1DS619	18 RU	36	24	30	28.5	19" EIA	316SS	14 ga.	Mobile	209.07
Front		N4X422430-M1DS619	22 RU	42	24	30	28.5	19" EIA	316SS	14 ga.	Mobile	226.82
Front		N4X482430-M1DS619	25 RU	48	24	30	28.5	19" EIA	316SS	14 ga.	Mobile	286.59
Front		N4X542430-M1DS619	29 RU	54	24	30	28.5	19" EIA	316SS	14 ga.	Mobile	308.08
Front		N4X602430-M1DS619	32 RU	60	24	30	28.5	19" EIA	316SS	14 ga.	Mobile	328.61
Front		N4X662430-M1DS619	36 RU	66	24	30	28.5	19" EIA	316SS	14 ga.	Mobile	359.74
Front		N4X722430-M1DS619	39 RU	72	24	30	28.5	19" EIA	316SS	14 ga.	Mobile	379.36
Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front/Rear	24D	N4X242424-M2DS619	12 RU	24	24	24	21	19" EIA	316SS	14 ga.	Mobile	167.34
Front/Rear		N4X302424-M2DS619	15 RU	30	24	24	21	19" EIA	316SS	14 ga.	Mobile	188.72
Front/Rear		N4X362424-M2DS619	18 RU	36	24	24	21	19" EIA	316SS	14 ga.	Mobile	205.55
Front/Rear		N4X422424-M2DS619	22 RU	42	24	24	21	19" EIA	316SS	14 ga.	Mobile	223.13
Front/Rear		N4X482424-M2DS619	25 RU	48	24	24	21	19" EIA	316SS	14 ga.	Mobile	280.52
Front/Rear		N4X542424-M2DS619	29 RU	54	24	24	21	19" EIA	316SS	14 ga.	Mobile	301.95
Front/Rear		N4X602424-M2DS619	32 RU	60	24	24	21	19" EIA	316SS	14 ga.	Mobile	322.27
Front/Rear		N4X662424-M2DS619	36 RU	66	24	24	21	19" EIA	316SS	14 ga.	Mobile	351.93
Front/Rear		N4X722424-M2DS619	39 RU	72	24	24	21	19" EIA	316SS	14 ga.	Mobile	371.35
Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front/Rear	30D	N4X242430-M2DS619	12 RU	24	24	30	27	19" EIA	316SS	14 ga.	Mobile	184.52
Front/Rear		N4X302430-M2DS619	15 RU	30	24	30	27	19" EIA	316SS	14 ga.	Mobile	207.53
Front/Rear		N4X362430-M2DS619	18 RU	36	24	30	27	19" EIA	316SS	14 ga.	Mobile	225.98
Front/Rear		N4X422430-M2DS619	22 RU	42	24	30	27	19" EIA	316SS	14 ga.	Mobile	245.19
Front/Rear		N4X482430-M2DS619	25 RU	48	24	30	27	19" EIA	316SS	14 ga.	Mobile	309.37
Front/Rear		N4X542430-M2DS619	29 RU	54	24	30	27	19" EIA	316SS	14 ga.	Mobile	332.76
Front/Rear		N4X602430-M2DS619	32 RU	60	24	30	27	19" EIA	316SS	14 ga.	Mobile	355.03
Front/Rear		N4X662430-M2DS619	36 RU	66	24	30	27	19" EIA	316SS	14 ga.	Mobile	388.75
Front/Rear		N4X722430-M2DS619	39 RU	72	24	30	27	19" EIA	316SS	14 ga.	Mobile	410.11
Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front/Rear	36D	N4X242436-M2DS619	12 RU	24	24	36	33	19" EIA	316SS	14 ga.	Mobile	201.7
Front/Rear		N4X302436-M2DS619	15 RU	30	24	36	33	19" EIA	316SS	14 ga.	Mobile	226.33
Front/Rear		N4X362436-M2DS619	18 RU	36	24	36	33	19" EIA	316SS	14 ga.	Mobile	246.41
Front/Rear		N4X422436-M2DS619	22 RU	42	24	36	33	19" EIA	316SS	14 ga.	Mobile	267.25
Front/Rear		N4X482436-M2DS619	25 RU	48	24	36	33	19" EIA	316SS	14 ga.	Mobile	338.23
Front/Rear		N4X542436-M2DS619	29 RU	54	24	36	33	19" EIA	316SS	14 ga.	Mobile	363.57
Front/Rear		N4X602436-M2DS619	32 RU	60	24	36	33	19" EIA	316SS	14 ga.	Mobile	387.79
Front/Rear		N4X662436-M2DS619	36 RU	66	24	36	33	19" EIA	316SS	14 ga.	Mobile	425.57
Front/Rear		N4X722436-M2DS619	39 RU	72	24	36	33	19" EIA	316SS	14 ga.	Mobile	448.88
Door Access	Encl. Depth	Part Number	Rack U	H	W	D	Max. Span	Rack Type	Material	Matl. Thk.	Mounting	Encl. Weight
Front/Rear	42D	N4X242442-M2DS619	12 RU	24	24	42	39	19" EIA	316SS	14 ga.	Mobile	218.88
Front/Rear		N4X302442-M2DS619	15 RU	30	24	42	39	19" EIA	316SS	14 ga.	Mobile	245.14
Front/Rear		N4X362442-M2DS619	18 RU	36	24	42	39	19" EIA	316SS	14 ga.	Mobile	266.84
Front/Rear		N4X422442-M2DS619	22 RU	42	24	42	39	19" EIA	316SS	14 ga.	Mobile	289.31
Front/Rear		N4X482442-M2DS619	25 RU	48	24	42	39	19" EIA	316SS	14 ga.	Mobile	367.09
Front/Rear		N4X542442-M2DS619	29 RU	54	24	42	39	19" EIA	316SS	14 ga.	Mobile	394.37
Front/Rear		N4X602442-M2DS619	32 RU	60	24	42	39	19" EIA	316SS	14 ga.	Mobile	420.55
Front/Rear		N4X662442-M2DS619	36 RU	66	24	42	39	19" EIA	316SS	14 ga.	Mobile	462.39
Front/Rear		N4X722442-M2DS619	39 RU	72	24	42	39	19" EIA	316SS	14 ga.	Mobile	487.65

19" EIA Server Rack Enclosure

Accessories & Options



19" EIA Stainless Steel Rack Rails

Stainless steel vertical rack rails conform to 19" EIA-310 spacing to support standard rack-mount equipment inside the enclosure.



19" EIA Horizontal Busbar

A horizontal busbar mounts across the top of the rack rail assembly to provide a centralized grounding and bonding point for rack-mounted equipment.




Air Conditioner Hatch Door

A pre-cut hatch panel with integrated mounting frame accommodates a side-mount air conditioning unit without compromising the enclosure's weatherproof seal.



Air Conditioned Unit

A side-mount air conditioning unit maintains stable internal temperatures in high-heat or direct-sun installations.




Barrier Insulation

Interior insulation panels line the back wall and door to reduce heat transfer and condensation risk in outdoor and temperature-variable environments.



Contact Door Switch

A door-mounted contact switch detects open or closed status to trigger alarms, lighting, or remote monitoring systems when the enclosure is accessed.



Door Stopper / Ground Strap

Holds the door open at a fixed angle during servicing while maintaining a continuous ground path between the door and cabinet body.




Filtered Fans

A filtered fan assembly provides positive-pressure ventilation, drawing outside air through replaceable filter fan to cool internal components while blocking dust and debris.



Floor Mounting Kit

A steel base and anchor kit secures the enclosure to a concrete pad or raised floor with pre-drilled anchor points and leveling provisions.



Gasketed Cover / Gland Plate

A gasketed gland plate seals cable entry points at the enclosure floor while maintaining ingress protection rating across multiple conduit or cable pass-throughs.



Key Lockable Handle

A key-lockable handle restricts enclosure access to authorized personnel, available in keyed-alike or keyed-different configurations.




NEMA 4/4X Clamps and Lockable Hasp

Draw-action clamps distribute clamping force evenly around the door perimeter to maintain a watertight seal, with a lockable hasp for padlock compatibility.



Print Pocket

A door-mounted document pocket keeps wiring diagrams, equipment specs, or maintenance records accessible inside the enclosure for field reference.



Quad Outlet Box

A floor-mounted four-outlet power box provides convenient AC power distribution to rack-mounted equipment without external hardware.



Removable Lifting Pads

Threaded lifting eye bolts install into the enclosure top for rigging and crane lifts, then remove cleanly after installation to restore the flat-top profile.



Sunshield Cover

An extended metal canopy mounts over the enclosure top to shade the cabinet from direct solar load, reducing internal temperature rise in outdoor installations.



Window Glass Door (Non-UL Option)

A tempered glass window panel allows visual inspection of rack-mounted equipment status without opening the enclosure; not available on UL Listed configurations.